

The Multimage® II FC Light Cabinet

MULTIPLE APPLICATIONS

5 Position Filter Wheel




A motorized, 5 position filter wheel customized for your fluorescent applications.

Chromalight™ Multi-wavelength Illuminator



A versatile excitation source, optional for the FluorChem® family. For detailed application information, see page 13.

Adjustable Tray




A two-position sample holder brings your sample closer to the detection source, increasing the efficiency of light collection. Standard with FluorChem® systems.

White Light Table




A true white light source, for applications such as imaging Coomassie gels and colony plates. Conveniently folds up when not in use.



Camera

Each Alpha Innotech imaging system is designed around a camera selected to meet the applications in your laboratory. Superior camera technology drives each system to deliver excellent image quality.



Control Panel

Touch-panel controls light sources and filter selection.



Dual Epi UV Lights

An optional excitation source for use with multicolor Westerns or fluorescent plates. Single or dual wavelength.



Dual Epi White Lights

Side Epi white lights allow users to focus on samples or blots before imaging, as well as provide bright illumination for opaque samples.



Dual Wavelength UV Transilluminator

Two wavelengths of illumination allow for excitation of multiple fluorescent dyes. Hi/ low intensity settings control the strength of illumination. UV light is automatically shut off when door is open, protecting users from UV exposure. UV transilluminator easily slides in and out of cabinet.

